# AC Adapter Operating Instructions

These instructions provide details on using the Fujitsu FMWAC6A (US), FMWAC6B (UK), and FMWAC6C (Euro) AC adapters.

**Note:** The only difference between the three AC adapter models is a variation in the supplied AC power cords. These operating instructions are applicable to all three adapter models.

The AC adapter is designed for use with your Stylistic 3400 pen tablet. Note that the AC adapter can also be used with external battery chargers, docking stations, port replicators, and cradles designed for use with the system.

#### Caution

- This AC adapter is for indoor use only. Do not use where exposure to water or excessive moisture is possible.
- This AC adapter generates a magnetic field that can damage your floppy disk drive. Maintain a safe minimum distance (about 3 inches or 8 centimeters) between the AC adapter and your floppy disk drive.



FUJITSU

# Connecting the AC Adapter

To connect the AC adapter to your system:

- 1. Plug the DC power cord into the DC input connector on your pen tablet, port replicator, docking station, or cradle.
- 2. Plug the AC power cord into the AC adapter.
- 3. Plug the other end of the AC power cord into your AC wall outlet.
- 4. Confirm that the AC adapter is now supplying power to your pen tablet system or other device. Refer to the user documentation for your system, if necessary, to determine how your pen tablet indicates external power is connected.

You can now use your system with external power supplied by the AC adapter.

### Disconnecting the AC Adapter

To disconnect the AC adapter:

- 1. Disconnect the DC output cord from your pen tablet system or other device.
- 2. Unplug the AC adapter from your AC wall outlet.

# Troubleshooting

If the AC adapter is not supplying power to your pen tablet system, check the following:

- Ensure that power is supplied to your AC wall outlet.
- Ensure that the AC power cord is firmly plugged into the AC adapter and the AC wall outlet.
- Ensure that the DC Power Cord is firmly seated in the DC input connector.

# Specifications

Specifications for the AC adapter are shown in the following table.

Input	100-240 VAC 50-60 Hz 1.2 A max
Output	16 VDC, 3.36 A max
DC output plug polarity	Center: positive (+) Sleeve: negative (-)